

Colori® 2.0 Medium-sized to large dogs

Optimal measuring point:
ca. 1–3 cm (depending on
muzzle length) below the eyes.
For short muzzles: ca. 1–2 cm,
for long muzzles: ca. 2–3 cm.

4 FOREHEAD STRAP:

Measure from point **M** to the back of the head, slightly above the collar line.

5 NECK CIRCUMFERENCE:

Measure around the neck as if fitting a collar, but slightly higher up toward the ears (see illustration 1).

Please note that every dog's head shape is different, and all measurements serve as guidelines to help you find the best-fitting model.

2 MUZZLE CIRCUMFERENCE:

Place the measuring tape at measuring point **M** and wrap it around the muzzle, returning to point **M**. Your dog should be relaxed, with the mouth slightly open. Note down the measurement.

1 MUZZLE LENGTH:

Step 1: Measure from measuring point **M** to the tip of the nose. Then subtract about 1–3 cm — this gives you the required Colori® length.
Step 2: Note down the measurement and choose your Colori® model.

3 MUZZLE CIRCUMFERENCE (PANTING WIDTH):

Option 1: Measure the circumference when your dog is panting — from the tip of the nose around the chin. Note down the value and compare all three measurements with the Colori® size chart to choose the right model.

Option 2 (with simulation aid):
To simulate panting, carefully use an object such as a ball or Kong. Measure the circumference from the nose tip around the chin. Note the value and compare it with the Colori® size chart to select the correct model.
Note: All Colori® measurements refer to inner dimensions.

Our measurement guide serves as an orientation. The stated measurements are approximate values. Due to varying nose lengths, deviations cannot be ruled out.